



Alu Lite Infoline



 Deliver full template size Resolution 75-150 dpi Only JPG (JPEG) format No bleed No pre-press marks Only CMYK colors 	(Visible 94x202) (in full 1:1 size) (We only accept jpg format, full size layouts) (Strict full size only) (crop marks, scales) (not RGB or Pantone)
CHECK before uploading:	That layout measurements are correct to fit the system That the colors are vivid enough to appear (over 30% CMYK) That the resolution and picture quality are OK
NOTE:	TETRIX considers uploaded documents to fulfill requirements in accordance to these notes. No separate layout check is performed.




Alu Lite Infoline



- a) Connect the octagonal rods two-by-two, using the supplied threaded joints.b) Should the grooves in the rods not allign, simply loosen one rod half a turn and tighten the other rod.
- c) Connected the feet of your choice (round feet or slim feet)d) Attach the end caps

Connect two pairs of the longer beams using the supplied beam joints. Insert the plastic rails into the grooves of the remaining two beams. Attach these to the joint beams to form a square frame.



III.

Attach the frame to the rods with the short beams as shown in the picture. Fasten the print with the Velcro at the top, stretch out and fasten at the bottom.





Alu Lite Infoline parts list

		Amount Checked		
A BAR	octagonal rod 1000mm			
	beam 940mm, 240mm			
	lock			
	beam joint			
\bigcirc	end cap			
	M10 bolt			
C	M10 threaded joint			
٢	allen key			
ſ	torx key			
	print			



Alu Lite Infoline optional items

		Amount Checked			
round foot					
slim foot					
cookie table					

Date

Signature